SPECIFICATIONS Material: Silicone rubber conforms to AA-59588 Class III, GR50 (unless otherwise specified). Mounting Nut: Brass, black oxide Temperature Range: -94° F to $+400^{\circ}$ F (-70° C to $+204^{\circ}$ C). TOGGLE BOOT Pressure Range: Exceeds 15 psi internal and 1500 psi external. Operational Life: 50,000 actuations (minimum). Shelf Life: Excess of 25 years. Resistant to: Salt spray, sunlight, ozone, weather, fungus, and most acids and lubricating oils. Agency Recognition: UL & ULC Recognized to UL Std. 50 **CUSTOMER'S PANEL CUSTOMER'S BACKING FASTENER HEX** .625 [15.9] CUSTOMER'S TOGGLE SWITCH Ø 0.160 TOGGLE BOOT [4] CUSTOMER'S PANEL 0.437 PERMISSIBLE RUBBER [11] OVERLAY .005 [0.127] MAX. **CUSTOMER'S** BACKING FASTENER 15/32-32NS-2B SECTION A-A **CUSTOMER'S** TOGGLE SWITCH TOLERANCES: UNLESS OTHERWISE NOTED \pm 1/32 [\pm 0.793]. Α REVISED THREADS NOTATION FROM 1/2-32 TO 15/32-32 DAN LAW 10.10.12 REV. DESCRIPTION DATE MAXIMUM AND MINIMUM MEASURE-TITLE: ENG. S. GOK 03.04.09 MENTS ARE STATED DIRECTLY ON **BOOT TOGGLE SWITCH** DWN: S. GOK 03.04.09 EACH DIMENSION. **EXPOSED BAT (N-1030B 160 ID)** CHKD. MAT'L: SILICONE RUBBER KEN S. 10.10.12 conforms to A-A-59588, Gr.50 **SCALE** DWG.NO N1030B 160 ID FINISH: APM-HEXSEAL CORPORATION 3:1 **GRAY**