

P 469-206-4040 sales@inteliheat.com

Thermosafe Technologies LLC dba Inteliheat North America 624 Krona, Suite 115 Plano, TX 75074, U.S.A.

InteliHeat® Thermulate® Full Coverage 15-gallon (50 Liter) Drum Heating Jacket (HJNA/B/OR)

Our InteliHeat® Thermulate® HJB Full Coverage 15-gallon Drum Heating Jacket for non-hazardous ordinary locations is ideal for gentle heating and freeze protection depending on the severity of environmental conditions.

- Ideal for gently heating, will typically maintain materials around 95°F(35°C).
- Fixed internal thermostat: 122°F(50°C).
- Polyurethane coated black nylon used on both sides of the jacket (inner and outer) to ensure maximum wear resistance.
- High grade thermal insulation to reduce heat loss and increase efficiency while providing protection for the operator.
- Fitted with adjustable retaining straps and quick release buckles.
- Flexible conforms to the container wall providing optimal thermal coupling
- Delivers heat over a large surface area, minimizing the possibilities of damaging the product.
- Fit and forget, built to last no regular maintenance required.
- Safe to use 24/7.
- 7 ft. (2m) premium oil, water, and abrasion resistant power cable
- Fitted with NEMA 1-15P plug
- Double insulated product
- Ambient temperature: -40°F to +104°F (-40°C to +40°C)
- ETL approved to UL and CSA standards.
- Waterproof and custom sizes available.

To fit container: 15 Gallon / 50 Liter Thermostat: Fixed 50°C / Fixed 122°F Size: Circumference 43.25" – 49.25" / Height 18" (1100 – 1250mm / 460mm) 120 Volts 300 Watts Part Number: HJNA/B/OR/# /EC/120/300/50





PLQ004 09/22

Parent Company: LMK Thermosafe Ltd Haverhill, Suffolk CB9 7AA, United Kingdom www.lmkthermosafe.co.uk Registered in England No. 3959310 VAT No. GB 759 6388 64