

CA-T2T2-5M-22/3P-R-BBG**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**General ordering data**

Version	AC charging cable, Plug type - charging point: Type 2, Plug type - vehicle side: Type 2, Charging power, max.: 22 kW, Number of phases: 3, Rated current: 32 A, Cable length: 5 m, Cable type: regular
Order No.	2754390000
Type	CA-T2T2-5M-22/3P-R-BBG
GTIN (EAN)	4050118899108
Qty.	1 pc(s).

CA-T2T2-5M-22/3P-R-BBG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 3,380 g

Temperatures

Storage temperature	-40 °C...70 °C	Humidity at storage temperature	5 - 95% rel. humidity
Operating temperature	-30 °C...50 °C	Operating temperature, min.	-30 °C
Operating temperature, max.	50 °C		

Material data

Max. relative humidity during storage	95 %	Operating temperature, max.	50 °C
Operating temperature, min.	-30 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-40 °C		

System requirements

Type of communication to vehicle Control Pilot (CP),
Proximity Pilot / Plug
Present (PP)

Features

Protection degree IP54

Housing

Protection degree IP54

Approvals and norms

Approvals IEC 62196-1, IEC
62196-2, EN 50620

Classifications

ETIM 6.0	EC002897	ETIM 7.0	EC002897
ETIM 8.0	EC002897	ECLASS 9.0	27-14-47-05
ECLASS 9.1	27-14-47-05	ECLASS 10.0	27-14-47-05
ECLASS 11.0	27-14-47-05	ECLASS 12.0	27-14-47-05

Downloads

User Documentation [Safety notes](#)
[Safety notes](#)

Catalogues [Catalogues in PDF-format](#)

Data sheet

CA-T2T2-5M-22/3P-R-BBG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

