



### Material

Screws	M3.0 Steel Ni plated
Pin Header	Copper alloy , Ni plated
Housing	PBT , UL94V-0

### Electrical

Standard	UL	IEC
Rated Voltage	300V	450V
Rated current	20A	32A
Wire range	22-12AWG	4mm <sup>2</sup>
Contact Resistance	20mΩ	
Insulation resistance	500MΩ/DC500V	
Withstanding voltage	AC1600V/1Min	

### Other Data

Pitch/Poles [mm]/[P]	9.0/3P , 12P
Operating temperature [°C]	-30°C~+120°C
Torque	5.1Kgf.cm/0.5Nm/4.3Lb.in

Dimensions

