






DIM.	TOL
5mm DOWN	±0.2
5~20mm	±0.3
20~40mm	±0.4
40~60mm	±0.5
60~100mm	±0.8
100mm UP	±1.0

REVISIONS			
REV	DESCRIPTION	DATE	BY



DETAIL SCALE 5:1



MOUNTING HOLE

QMFZ2 Component - Plastics
 TELIN CHEMICALS LTD
 HIBIYA DAIBIRU BLDG 2-2 UCHISAIWAI-CHO 1-CHOME CHIYODA-KU TOKYO 100-0011 JAPAN
 Material Designation: L-1225(H)(Z)
 Product Description: Polycarbonate (PC), designated "Parlite" furnished as pellets, powder.

Color	Min. Thick. (mm)	Flame Class	HWI	HAI	RTI Elec	RTI Imp	RTI Str	IBC GWIT	IBC GWFI
ALL	0.4	V-2	4	3	80	80	80	-	-
	0.75	V-2	3	1	80	80	80	-	-
	1.5	V-2	3	1	125	115	125	-	-
	1.9	HB	3	1	125	115	125	-	-
	3	HB	2	1	125	115	125	-	-
	6	HB	1	1	125	115	125	-	-
	CTI: 2	HVTR: 4			D495: 5				

Dielectric Strength (kV/mm): 30
 Volume Resistance (10¹²ohm-cm): 15
 ISO Tensile Strength (MPa): -
 ISO Flexural Strength (MPa): -
 ISO Tensile Impact (kJ/m²): -
 ISO Izod Impact (kJ/m²): -
 (H)
 (Z)

Material designation may be suffixed with any one or two letters.
 Subjected to one or more of the following tests: Ultraviolet Light, Water Exposure or Immersion in accordance with UL 746C, where the acceptability for outdoor use is to be determined by UL Inc.

IBC Ball Pressure (Co): -
 Dimensional Stability (%): 0
 ISO Heat Deflection (Co): -
 ISO Charpy Impact (kJ/m²): -

Report Date: 2/10/1989

Underwriters Laboratories Inc®

<p>康揚企業股份有限公司 KANG YANG HARDWARE ENTERPRISE CO., LTD. 康揚塑膠(東莞)有限公司 KANG YANG PLASTIC(DONG GUAN) CO., LTD. 康哲電腦配件(吳江)有限公司 KANG CHEE COMPUTER COMPONENTS(WUJIANG) CO., LTD.</p>		TITLE	LIGHT PIPE	SPEC. DWG.	
		MATERIAL	PC UL94V-2	DATE	2008.10.03
PART NUMBER		LPE1-5-20.5	DRAWING NUMBER	LPE1-5-20.5	
SIZE	A4	SCALE	2:1	UNIT	mm
REV	A	COLOR	CLEAR	CHECK	
UNLESS OTHERWISE SPECIFIED TOLERANCE		SEE ABOVE	APPROVED		