





PRODUCT NO.	DIM "L"
73255-101	2
-101LF	
73255-102	4.5
-102LF	



SECT X-X'



RECOMMENDED PCB LAYOUT (2/1)

No.	DESCRIPTION	MATERIAL	FINISH
1	SHELL	BRASS	Au 0.05um MIN.
2	INNER CONTACT	BERYLLIUM COPPER	Au 0.8um MIN.
3	OUTER CONTACT	BERYLLIUM COPPER	Au 0.8um MIN.
4	INSULATOR	PTFE	

NOTE

- FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

mat'l. code				surface	tolerance	projection	product family	CODE
---				ISO 1302	ISO 406	ISO 1101	METRAL	JP
ltr	description	ecn no	dr	date	tolerances unless otherwise specified		title	
A	RELEASED	J80415	Y.K	10/12/98	angles	linear	MM	
B	REVISED	J20641	Y.K	12/16/02	0°±3'	0.XX ±0.2	scale 5:1	
C	REVISED	J05-0675	T.S	10/21/05	0°±3'	0.XX ±0.2		
D	REVISED	J07-0030	S.O	1/18/07	dr	Y.KODAIRA	10/12/98	
					enrg	S.OKUDAIRA	1/18/07	
					chr	R. Shoup	1/18/07	
					appd	J. Anderson	1/18/07	
sheet	revision						dwg no	sheet 1 of 1 size
index	sheet						73255	A4
							type	Customer Drawing
								Rev. D