

HG 2620 E

Powerful. Tough. Robust.

Technical Specifications

Power supply: 120 VAC, 50/60 Hz
Output: 1750 W
Temperature: 120 - 1300° F
Temperature setting: Infinitely variable in 10° F steps by toggle
Thermal cutout: Yes
Airflow rate: 2 – 13 cfm (+/- 0.5 cfm)
Air pressure: 3,000 Pa

Features: Display in field of vision, plug-in heating element, ergonomic grip, safety heat indicator, fine dust filter, 4 memory programs, digital display, field changeable power cord, LOC function, restart protection.

Applications: Suitable for construction site use

Motor: Brushless
Motor life: 10,000 hours
Heating element: Ceramic heating element

Weight: 1.85 lbs.
Dimensions: 14.10" x 3.60" x 3.70"
(L x W x D)
Warranty: 1 year



UPC Code	Product No.
018139376002	110025600