




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF AMPHENOL LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY AMPHENOL LTW.




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	C191760	2019/10/15	Jane	X5
D	C192018	2019/11/15	Vicky	X4
E	C231240	2023/09/22	Ruru	X2



BB-XXBMMA-QL8XPP
 XX: No. Of Pin
 S: With Red Color Seal 1, Cable OD 5.0~6.0mm.
 M: With Yellow Color Seal 2, Cable OD 6.0~8.0mm.
 L: With Blue Color Seal 3, Cable OD 8.0~10.0mm.
 A: With Seal 1 & Seal 2 & Seal 3.



Pin Assignments Front View



2 Pin

3 Pin

4 Pin

Note:
 * \varnothing Important Dimension
 * Waterproof Rate: IP68, mated 1m/24h
 * Housing: Thermoplastic, Black
 * Pin: Copper Alloy, Gold Plated
 * Clamp Ring: Thermoplastic, Black
 * Sealing Nut: Thermoplastic, Black
 * Seals: Rubber
 * One set unassembled in one pe bag

UNIT:mm		TITLE	XLOK, B-10A, CABLE W/O SR M, M, FI CRIMP, XLOK	
TOLERANCE	$\pm 0.5mm$	SCALE	1:1	SIZE A4
		REV.	E	WC-REV. A.5
				\varnothing : Inspection item

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Brady Chung	2019-09-24
DWG NO	CHECKED BY	DATE
BB-XXBMMA-QL8XPP	Jane Wang	2019-09-24
CUSTOMER	APPROVED BY	DATE
ALTW	Neo Tsai	2019-09-24