

## Detailed Specifications

<b>Frame Width:</b>	40[mm]
<b>Frame Height:</b>	40[mm]
<b>Frame Depth:</b>	10[mm]
<b>Max. Air Flow:</b>	4.9[CFM]
<b>Max. Air Flow:</b>	0.14[m <sup>3</sup> per min]
<b>Max. Static Pressure:</b>	0.11[In H <sub>2</sub> O]
<b>Max. Static Pressure:</b>	27.5[Pa]
<b>Fan Speed:</b>	5500[RPM]
<b>Noise:</b>	21[dB]
<b>Life Expectancy:</b>	40 degree C 30,000 Hours[L10]
<b>Bearing Type:</b>	Sleeve Bearing
<b>Nominal Voltage:</b>	5[V]
<b>Operating Voltage - Lower:</b>	4.5[V]
<b>Operating Voltage - Upper:</b>	5.5[V]
<b>Current:</b>	0.09[A]
<b>Input Power:</b>	0.5[W]
<b>Mass:</b>	16[g]
<b>Tach / Locked Rotor Output:</b>	No
<b>Status:</b>	Active