


Vishay High Power Products

HEXFRED® Ultrafast Soft Recovery Diode, 2 x 8 A



PRODUCT SUMMARY					
V_{R}	600 V				
V _F at 8 A at 25 °C	1.7 V				
I _{F(AV)}	2 x 8 A				
t _{rr} (typical)	18 ns				
T _J (maximum)	150 °C				
Q _{rr}	65 nC				
dI _{(rec)M} /dt	240 A/μs				

FEATURES

- Ultrafast recovery
- · Ultrasoft recovery
- Very low I_{RRM}
- Very low Q_{rr}
- · Specified at operating conditions
- · Designed and qualified for industrial level

BENEFITS

- · Reduced RFI and EMI
- · Reduced power loss in diode and switching transistor
- · Higher frequency operation
- · Reduced snubbing
- · Reduced parts count

DESCRIPTION

HFA16TA60C is a state of the art center tap ultrafast recovery diode. Employing the latest in epitaxial construction and advanced processing techniques it features a superb combination of characteristics which result in performance which is unsurpassed by any rectifier previously available. With basic ratings of 600 V and 8 A per leg continuous current, the HFA16TA60C is especially well suited for use as the companion diode for IGBTs and MOSFETs. In addition to ultrafast recovery time, the HEXFRED® product line features extremely low values of peak recovery current (I_{RRM}) and does not exhibit any tendency to "snap-off" during the t_b portion of recovery. The HEXFRED features combine to offer designers a rectifier with lower noise and significantly lower switching losses in both the diode and the switching transistor. These HEXFRED advantages can help to significantly reduce snubbing, component count and heatsink sizes. The HEXFRED HFA16TA60C is ideally suited for applications in power supplies and power conversion systems (such as inverters), motor drives, and many other similar applications where high speed, high efficiency is needed.

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Cathode to anode voltage	V_{R}		600	V	
Maximum continuous forward current per leg	I _F	T _C = 100 °C	8		
per device			16	Α	
Single pulse forward current	I _{FSM}		60	A	
Maximum repetitive forward current	I _{FRM}		24		
Maximum power dissipation	P _D	T _C = 25 °C	36	W	
waximum power dissipation		T _C = 100 °C	14	VV	
Operating junction and storage temperature range	T _J , T _{Stg}		- 55 to + 150	°C	

Document Number: 93072 Revision: 29-Jul-08

HFA16TA60C

Vishay High Power Products

HEXFRED® Ultrafast Soft Recovery Diode, 2 x 8 A



ELECTRICAL SPECIFICATIONS PER LEG (T _J = 25 °C unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS	TEST CONDITIONS		TYP.	MAX.	UNITS
Cathode to anode breakdown voltage	V _{BR}	Ι _R = 100 μΑ		600	-	-	
		I _F = 8 A		-	1.4	1.7	V
Maximum forward voltage V _{FM}	I _F = 16 A	See fig. 1	-	1.7	2.1		
		I _F = 8 A, T _J = 125 °C		-	1.4	1.7	
Maximum reverse		$V_R = V_R$ rated	See fig. 2	-	0.3	5.0	
leakage current	I _{RM}	$T_J = 125 ^{\circ}\text{C}, V_R = 0.8 \text{x} V_R \text{rated}$	See lig. 2	-	100	500	μΑ
Junction capacitance	C _T	V _R = 200 V	See fig. 3	=	10	25	pF
Series inductance	L _S	Measured lead to lead 5 mm from package body - 8.0 -		nH			

DYNAMIC RECOVERY CHARACTERISTICS PER LEG (T _J = 25 °C unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNITS
	t _{rr}	I _F = 1.0 A, dI _F /dt = 200 A/μs, V _R = 30 V		-	18	-	
Reverse recovery time See fig. 5 and 10	t _{rr1}	T _J = 25 °C		-	37	55	ns
ood lig. o und 10	t _{rr2}	T _J = 125 °C	I _F = 8.0 A	-	55	90	
Peak recovery current	I _{RRM1}	T _J = 25 °C		-	3.5	5.0	А
See fig. 6	I _{RRM2}	T _J = 125 °C		-	4.5	8.0	
Reverse recovery charge	Q _{rr1}	T _J = 25 °C	dI _F /dt = 200 A/μs	-	65	138	nC
See fig. 7	Q _{rr2}	T _J = 125 °C	V _R = 200 V	-	124	360	iiC
Peak rate of fall recovery current during t _b	dI _{(rec)M} /dt1	T _J = 25 °C		-	240	-	A/μs
See fig. 8	dI _{(rec)M} /dt2	T _J = 125 °C		-	210	-	Α/μδ

THERMAL - MECHANICAL SPECIFICATIONS PER LEG						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Lead temperature	T _{lead}	0.063" from case (1.6 mm) for 10 s	-	-	300	°C
Junction to case, single leg conducting	Б		-	-	3.5	
Junction to case, both legs conducting	R _{thJC}		-	-	1.75	K/W
Thermal resistance, junction to ambient	R _{thJA}	Typical socket mount	-	-	80	- N/VV
Thermal resistance, case to heatsink	R _{thCS}	Mounting surface, flat, smooth and greased	-	0.5	-	
Maight			-	2.0	-	g
Weight			-	0.07	-	OZ.
Mounting torque			6.0 (5.0)	-	12 (10)	kgf · cm (lbf · in)
Marking device		Case style TO-220AB		HFA16	TA60C	•

Document Number: 93072 Revision: 29-Jul-08



HEXFRED® Vishay High Power Products Ultrafast Soft Recovery Diode, 2 x 8 A




Fig. 1 - Maximum Forward Voltage Drop vs. Instantaneous Forward Current (Per Leg)




Fig. 2 - Typical Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance ZthJC Characteristics (Per Leg)

Vishay High Power Products

HEXFRED® Ultrafast Soft Recovery Diode, 2 x 8 A






Fig. 5 - Typical Reverse Recovery Time vs. dl_F/dt (Per Leg)




Fig. 7 - Typical Stored Charge vs. dl_F/dt (Per Leg)




Fig. 6 - Typical Recovery Current vs. dl_F/dt (Per Leg)




Fig. 8 - Typical $dI_{(rec)M}/dt$ vs. dI_F/dt (Per Leg)



HEXFRED® Vishay High Power Products Ultrafast Soft Recovery Diode, 2 x 8 A





Fig. 9 - Reverse Recovery Parameter Test Circuit



- (1) dl_F/dt rate of change of current through zero crossing
- (2) I_{RRM} peak reverse recovery current
- $\begin{array}{l} \text{(3) } \textbf{t}_{\text{rr}} \text{ reverse recovery time measured} \\ \text{from zero crossing point of negative} \\ \text{going I}_{\text{F}} \text{ to point where a line passing} \\ \text{through 0.75 I}_{\text{RRM}} \text{ and 0.50 I}_{\text{RRM}} \\ \text{extrapolated to zero current.} \end{array}$
- (4) \mathbf{Q}_{rr} area under curve defined by \mathbf{t}_{rr} and \mathbf{I}_{RRM}

$$Q_{rr} = \frac{t_{rr} \times I_{RRM}}{2}$$

(5) $dI_{(rec)M}/dt$ - peak rate of change of current during t_b portion of t_{rr}

Fig. 10 - Reverse Recovery Waveform and Definitions

LINKS TO RELATED DOCUMENTS					
Dimensions http://www.vishay.com/doc?95222					
Part marking information	http://www.vishay.com/doc?95225				



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com