

FO connectors - VS-V1-C-SCRJ-MNNA-PG9-B1-G - 1419188

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



SCRJ fiber optic connector, IP67, with bayonet locking, metal housing, duplex, with adhesive connection technology, for single-mode fiber, for cable diameter of 5.0 mm ... 10 mm



EtherNet/IP

Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	160.0 GRM
Custom tariff number	85366990
Country of origin	Germany

Technical data

Mechanical characteristics

Number of positions	2
Number of slots	1
Locking type	Bayonet locking
Fiber type	Single mode fiberglass
Insertion/withdrawal cycles	500
Connection method	SC duplex
Max. cable diameter	5 mm ... 10 mm
Color	silver

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Degree of protection	IP67

Material data

Housing material	Zinc die-cast
Material	Metal

FO connectors - VS-V1-C-SCRJ-MNNA-PG9-B1-G - 1419188

Technical data

Electrical characteristics

Number of positions	2
---------------------	---

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260709
eCl@ss 7.0	27440305
eCl@ss 8.0	27440305

ETIM

ETIM 2.0	EC001122
ETIM 3.0	EC001122
ETIM 4.0	EC001122
ETIM 5.0	EC001122

UNSPSC

UNSPSC 6.01	30211832
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121429

Approvals

Approvals

Approvals

GOST / GOST

Ex Approvals

Approvals submitted

FO connectors - VS-V1-C-SCRJ-MNNA-PG9-B1-G - 1419188

Approvals

Approval details

GOST 

GOST 

Drawings

Dimensioned drawing

