




MALE RECEPTACLE SMT EDGE CARD-TR500

PAGE 1/4 ISSUE 08-04-20A SERIES SMPM-L PART NUMBER R201L00010 Ref. Plane 6.18 Ø4 3 В 9.7 3.18 4.4 1.42 DÉTAIL B ECHELLE 12 : 1 3.6 Center of gravity 0.18 Scale: 1/1

All dimensions are in mm. Tolerances according ISO 2768 m-H





# **Technical Data Sheet**

MALE RECEPTACLE SMT EDGE CARD-TR500

PAGE 2/4 ISSUE 08-04-20A SERIES SMPM-L PART NUMBER R201L00010

#### **PACKAGING**

| Standard | Unit       | Tape Reel |
|----------|------------|-----------|
| 100      | Contact us | 500       |

## **ELECTRICAL CHARACTERISTICS**

Impedance Ω Frequency 0-65 GHz 0,0000 x F(GHz) Maxi **VSWR** √F(GHz) dB Maxi Insertion loss \*.012 RF leakage - F(GHz)) dB Maxi **TBD** Voltage rating 125 Veff Maxi Dielectric withstanding voltage 250 Veff mini Insulation resistance 5000  $M\Omega$  mini

#### **MECHANICAL CHARACTERISTICS**

Center contact retention

 Axial force – Mating End
 6.7
 N mini

 Axial force – Opposite end
 6.7
 N mini

 Torque
 NA
 N.cm mini

Recommended torque

Mating NA N.cm NA N.cm

Mating life 500 Cycles mini
Nominal Weight 0,5120 g

(Add +15% for max

weight)

#### RECOMMENDED SOLDERING PARAMETERS

Solder paste deposit: Sn (96.5) - Ag (3.0) - Cu (0.5)

Granulometry from 25 to 36 micrometer Deposit thickness: 100 micrometer

Flux: low residue

Soldering T°C according to IEC 61760-1

and max 10s at max 260°C

### **ENVIRONMENTAL**

Operating temperature -65/+165 °C Hermetic seal NA Atm.cm3/s Panel leakage

# **SPECIFICATION**

## **OTHER CHARACTERISTICS**

Assembly instruction:

#### Others

- \* 1.15 (DC-26.5 GHz) 1.35 (26.5-40 GHz)
- \* Coaxial transmission line only
- \* RF performances highly depend on PCB adaptation


# CUSTOMER'S APPROVAL Department or Company's stamp Name: Date: Copy to send back to RADIALL S.A BEFORE:







MALE RECEPTACLE SMT EDGE CARD-TR500

PAGE 3/4 ISSUE 08-04-20A SERIES SMPM-L PART NUMBER R201L00010





# **PCB Dimension**







MALE RECEPTACLE SMT EDGE CARD-TR500

PAGE 4/4 ISSUE 08-04-20A SERIES SMPM-L PART NUMBER R201L00010

# **PACKAGING**

