



General ordering data

Order No.	1789960000
Part designation	HDC S4 0 SAS
Version	HDC insert, Pin, 830 V, 80 A, Poles: 4 + 0 + PE, Axial screw connection, Size: 6
EAN	4032248212026
Qty.	10 pc(s).

Product notes

Note, accessories	Use spanner size 3 AF for axial screw connection For additional accessories, refer to Accessories chapter.
-------------------	---

Dimensions

High plug B	43.9 mm
Total length A	84.5 mm

General data

Colour	beige
Insulating material group	IIIa
Insulation material	PC glass-fibre reinforced (UL-listed and railway-certified)
Insulation resistance	$10^{10} \Omega$
No. of poles, total	4 + 0 + PE
Plugging cycles, silver	≥ 500
Pollution severity	3
Temperature, max.	125 °C
Temperature, min.	-40 °C
UL 94 flammability class	V-0
Size	6
Series	MixMate
Type	Pin
Type designation	S4/0

Connection data PE

Rated cross-section	16 mm ²
Fixing screw	M 5
Min. tightening torque	2 Nm
Blade size, crosshead	size PZ2
Max. tightening torque	2.5 Nm
Blade size, slotted	SD 0.8 x 4.0
Stripping length	8 mm
Max. connection cross-section, solid	1.5 mm ²
Min. connection cross-section, solid	16 mm ²
Min. connection cross-section, stranded	1.5 mm ²
Connection type PE	Screw connection
Max. connection cross-section, stranded	16 mm ²
Min. connection cross-section "f" with wire end ferrule	1.5 mm ²
Max. connection cross-section "f" with wire end ferrule	16 mm ²
AWG, min.	AWG 16
AWG, max.	AWG 6

Rating data

Rated voltage (DIN EN 61984)	830 V
Rated current (DIN EN 61984)	80 A
Rated voltage according to UL/CSA	600 V AC/DC
Rated impulse voltage (DIN EN 61984)	8 kV

Version

Type of connection	Axial screw connection
Min. tightening torque	2 Nm
Max. tightening torque	3 Nm
Stripping length	13 mm
Material	copper alloy
Connection cross-section, min.	1.5 mm ²
Connection cross-section, max.	16 mm ²
AWG, min.	AWG 16

Version

AWG, max.	AWG 6
Size	6
Surface finish	Silver passivated
Volume resistance	≤ 4mΩ
Clamping screw	M 10 x 1 mm

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC001121
ETIM 3.0	EC001121
eClass 4.1	27-14-08-05
eClass 5.0	27-14-34-19
eClass 5.1	27-14-34-19

Similar products

Order No.	Part designation	Version
1789970000	HDC S4 0 BAS	HDC insert, Socket, 830 V, 80 A, Poles: 4 + 0 + PE, Axial screw connection, Size: 6
1789980000	HDC S4 BAS	HDC insert, Socket, 1000 V, 65 A, Poles: 4 + PE, Axial screw connection, Size: 3
1789990000	HDC S4 SAS	HDC insert, Pin, 1000 V, 65 A, Poles: 4 + PE, Axial screw connection, Size: 3
1790010000	HDC S6 12 BAS	HDC insert, Socket, 630 V, 48 A, Poles: 6 + 12 + PE, Axial screw connection, Size: 6
1790000000	HDC S6 12 SAS	HDC insert, Pin, 690 V, 48 A, Poles: 6 + 12 + PE, Axial screw connection, Size: 6
1790020000	HDC S6 6 BAS	HDC insert, Socket, 690 V, 100 A, Poles: 6 + 6 + PE, Axial screw connection, Size: 8
1790030000	HDC S6 6 SAS	HDC insert, Pin, 690 V, 100 A, Poles: 6 + 6 + PE, Axial screw connection, Size: 8