

LUMOTAST 25 - Illuminated pushbutton with flush lens, "Click' quick-assembly feature, housing

1.15.150.506/0000

Note when using LEDs: A notch on the lamp socket identifies the cathode side.

Please include the desired lens in your order.





General information	
Form of lens	flat lens
Form of collar	square
Dimensions	
Length of collar	25 mm
Width of collar	25 mm
Overall height	7.1 mm
Mounting depth with connector	30.7 mm
Mounting depth with plug-in socket	33.4 mm
Mounting hole	16.2 mm
Mechanical design	
Mounting	click quick connection
Terminals	pin connector 4-pole / plug-in socket
Contact system	snap-action contact
Contact function	momentary
Contact arrangement	1 NO
Contact materials	Au
Illumination	yes
Lamp socket	Bi-Pin T1 / T1¼
Mechanical characteristics	
Operating force max.	<u>6 N</u>
Operating travel	3 mm
Switching travel	2 mm
Robustness max.	100 N
Electrical characteristics	
Rated voltage AC/DC max.	35 V
Rated voltage AC/DC min.	0.02 V
Rated current AC/DC max.	100 mA
Rated current AC/DC min.	0.01 mA
Contact resistance acc. to life max.	100 mΩ
Bouncing time max.	5 ms




Other specifications	
Operating life (operations)	1,000,000 cycle
Degree of protection from front side	IP65 (DIN EN 60529)
Ambient temp. operating max. without lamp / LED	-25 °C
Ambient temp. operating max. without lamp / LED	+70 °C
Ambient temp. operating min. with lamp /LED	-25 °C
Ambient temp. operating max. with lamp /LED	+55 °C
Storage temperature min.	-40 °C
Storage temperature max.	+80 °C
Environmental restistance	acc. to IEC 60068-2-14, -30, -33 and -78
Weight	7 g
ROHS compliant	yes
REACH compliant	yes


Panel cut-out











with socket connector

