

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Polyamide protective hose, inflammability class HB, UV resistant

Image shows WP-PA HF-HB 10.0 BK version

## **Key Commercial Data**

Packing unit	1 M
Minimum order quantity	50 M
Custom tariff number	39173200
Country of origin	Germany

#### Technical data

#### **Dimensions**

Inner diameter (f)	12.00 mm
Outside diameter	15.80 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C 105 °C
Short-term temperature	120 °C

#### General

Color	black
Туре	Helically corrugated plastic hose
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	НВ
Material	PA
Bending radius, static	35.00 mm
Bending radius, dynamic	55.00 mm

## Standards and Regulations

Resistance to UV radiation	yes
Halogen-free	yes



## Technical data

## Standards and Regulations

Connection in acc. with standard	UL
Flammability rating according to UL 94	НВ

## Classifications

## eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27430304

## **ETIM**

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177

## **UNSPSC**

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

## Approvals

Approvals

UL Recognized / VDE Zeichengenehmigung

Ex Approvals

Approvals submitted



## Approvals

Approval details

UL Recognized **5** 

VDE Zeichengenehmigung



## Accessories

Accessories

Corrugated pipe screw connection

Screw connection - WP-G HF IP66 PG11 BK - 3240890



Cable gland, Pg thread, IP66 protection, straight

Screw connection - WP-G HF IP66 M16 BK - 3240897



Cable gland, metric thread, IP66 protection, straight

Screw connection - WP-G HF IP69K PG11 BK - 3240876



Cable gland, Pg thread, IP68/69k protection, straight



## Accessories

Screw connection - WP-G HF IP69K M16 BK - 3240883



Cable gland, metric thread, IP68/69k protection, straight

Screw connection - WP-GA HF IP66 PG11 BK - 3240918



Cable gland, Pg thread, IP66 protection, angled

Screw connection - WP-GA HF IP66 M16 BK - 3240925



Cable gland, metric thread, IP66 protection, angled

Screw connection - WP-GA HF IP69K PG11 BK - 3240904



Cable gland, Pg thread, IP68/69k protection, angled

Screw connection - WP-GA HF IP69K M16 BK - 3240911



Cable gland, metric thread, IP68/69k protection, angled



## Accessories

Screw connection - WP-GR HF IP66 PG11 BK - 3240946



Cable gland, Pg thread, IP66 protection, with strain relief

Screw connection - WP-GR HF IP66 M16 BK - 3240953



Cable gland, metric thread, IP66 protection, with strain relief

Screw connection - WP-GR HF IP69K PG11 BK - 3240932



Cable gland, Pg thread, IP68/69k protection, with strain relief

Screw connection - WP-GR HF IP69K M16 BK - 3240939



Cable gland, metric thread, IP68/69k protection, with strain relief

## Mounting material

Hose holder with cover - WP-BASE C PA HF 15,8 BK - 3240960



Hose holder with cover



## Accessories

Hose clamp - WP-BASE HF 15,8 - 3240968



Hose clamps

Protective hose fixing bracket - WP-BASE A M16 - 3241083



Fixing bracket for protective sleeves, fixed with two screws

## Protective cap

Transition sleeve from hose to cable - WP-EC TPE HF 15,8 BK - 3240976



End sleeves, transition sleeves, from hose to cable

Cable protection end sleeve - WP-SC PA HF 15,8 BK - 3240983



End sleeves as cable protection

Phoenix Contact 2016 @ - all rights reserved http://www.phoenixcontact.com