

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)

Polyamide protective hose, inflammability class HB, UV resistant



Image shows WP-PA HF-HB 10.0 BK version

Key Commercial Data

Packing unit	1 M
Minimum order quantity	50 M
Custom tariff number	39173200
Country of origin	Germany

Technical data

Dimensions

Inner diameter (f)	16.50 mm
Outside diameter	21.20 mm

Ambient conditions

Ambient temperature (operation)	-40 °C 105 °C
Short-term temperature	120 °C

General

Color	black
Туре	Helically corrugated plastic hose
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	НВ
Material	РА
Bending radius, static	45.00 mm
Bending radius, dynamic	75.00 mm

Standards and Regulations

Resistance to UV radiation	yes
Halogen-free	yes

07/28/2016 Page 1 / 6



Technical data

Standards and Regulations

Connection in acc. with standard	UL
Flammability rating according to UL 94	HB

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27430304

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

UL Recognized / VDE Zeichengenehmigung

Ex Approvals

Approvals submitted



Approvals

Approval details

UL Recognized 🔊

VDE Zeichengenehmigung

Accessories

Accessories

Corrugated pipe screw connection

Screw connection - WP-G HF IP66 PG16 BK - 3240891



Cable gland, Pg thread, IP66 protection, straight

Screw connection - WP-G HF IP66 M20 BK - 3240898



Cable gland, metric thread, IP66 protection, straight

Screw connection - WP-G HF IP69K PG16 BK - 3240877



Cable gland, Pg thread, IP68/69k protection, straight

07/28/2016 Page 3 / 6



Accessories

Screw connection - WP-G HF IP69K M20 BK - 3240884



Cable gland, metric thread, IP68/69k protection, straight

Screw connection - WP-GA HF IP66 PG16 BK - 3240919



Cable gland, Pg thread, IP66 protection, angled

Screw connection - WP-GA HF IP66 M20 BK - 3240926



Cable gland, metric thread, IP66 protection, angled

Screw connection - WP-GA HF IP69K PG16 BK - 3240905



Cable gland, Pg thread, IP68/69k protection, angled

Screw connection - WP-GA HF IP69K M20 BK - 3240912



Cable gland, metric thread, IP68/69k protection, angled

07/28/2016 Page 4 / 6



Accessories

Screw connection - WP-GR HF IP66 PG16 BK - 3240947



Cable gland, Pg thread, IP66 protection, with strain relief

Screw connection - WP-GR HF IP66 M20 BK - 3240954



Cable gland, metric thread, IP66 protection, with strain relief

Screw connection - WP-GR HF IP69K PG16 BK - 3240933



Cable gland, Pg thread, IP68/69k protection, with strain relief

Screw connection - WP-GR HF IP69K M20 BK - 3240940



Cable gland, metric thread, IP68/69k protection, with strain relief

Mounting material

Hose holder with cover - WP-BASE C PA HF 21,2 BK - 3240961



Hose holder with cover



Accessories

Hose clamp - WP-BASE HF 22 - 3240970



Hose clamps

Protective hose fixing bracket - WP-BASE A PG16 - 3241079



Fixing bracket for protective sleeves, fixed with two screws

Protective cap

Transition sleeve from hose to cable - WP-EC TPE HF 21,2 BK - 3240977



End sleeves, transition sleeves, from hose to cable

Cable protection end sleeve - WP-SC PA HF 21,2 BK - 3240984



End sleeves as cable protection

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com