## Pushbutton non-illuminated - mounting hole diameter 15.2 mm, quick-connect terminals, 1 NO, green 1.10.001.011/0507



▲


General information	-
Form of lens	protruding lens
Color of lens	opaque green
Form of collar	round
Dimensions	
Dimensions	
Diameter of collar	<u>19 mm</u>
Overall height	8.2 mm
Mounting depth	21.5 mm
Mounting hole	15.2 mm
Mechanical design	
Mounting	ring nut
Terminals	solder/quick connector 6.3x0.8 / 2x 2.8x0.8mm
Contact system	bridge contact
Contact function	momentary
Contact arrangement	1 NO
Contact materials	Ag
Illumination	no
Lamp socket	no
Mechanical characteristics	
Operating force max.	7.5 N
Operating travel	<u>3 mm</u>
Switching travel NC	1.2 mm
Switching travel NO	2.0 mm
Robustness max.	100 N
Electrical characteristics	
Rated voltage AC max.	250 V
Rated current max.	0.7 A
Contact resistance when new max.	 50 mΩ
Contact resistance acc. to life max.	300 mΩ
Other specifications	
Operating life (operations)	25,000 cycle
Degree of protection from front side	IP40 acc. to DIN EN 60529 (IP65 with sealing cap)
Operation temperature min.	-25 °C
Ambient temp. operating max.	+85 °C
Storage temperature min.	-40 °C

Technical data are approximate and intended solely for general orientation in the selection of a product. Subject to modifications and errors. Images and other graphics may only be similar. For more information, refer to www.rafi.de chapter Imprint / Data Protection.



Storage temperature max.	+90 °C
Environmental resistance	acc. to IEC 60068-2-14, -30, -33 and -78
Weight	_7 g
Approvals	ENEC T 85/55
Flame class acc. to UL 94	V 0
Hot wire ignition acc. to IEC 60695-2-1	yes
ROHS compliant	yes
REACH compliant	yes

## Panel cut-out



## screw terminals

