**Aven Inc.** 4595 Platt Rd. Ann Arbor, MI 48108 **Phone:** 734.973.0099

Email: info@aventools.com • Web Address: www.aventools.com

All Categories > Optical Inspection Tools > CCD/CMOS Cameras > Digital Cameras > Aven MiniVue USB Digital Color Camera > Item # 26100-230



# Item # 26100-230, MiniVue Camera

### Accessories included are:-

- USB Shutter Cable
- USB Cable
- TV-Out Cable
- SD Card
- Remote
- Power Supply
- Image Capture Software

### Features · Specifications

### **Features**

- 3.1 Megapixel Camera
- Built in High Resolution 2" Screen
- Full Digital Signal Processing
- Capture Images and Video on the built in SD Card and transfer to a PC at your convenience
- Connect via USB to a PC or Printer
- Friendly User Interface
- Crosshair feature for location and measurement
- TV Out allows the connection of an external LCD monitor for detailed viewing
- Wireless and wired USB Shutter control
- Many stand alone features on camera

# **Specifications**

Sensor Resolution	3.1 megapixels
Max. Resolution	8 megapixels
Sensor Type	1/2" CMOS
Frame Rate	28 fps at TV/PC Out
LCD Screen Size	2 in
Memory Card	SD/MMC Card
TV Output	NTSC/PAL
USB Interface	Yes
Controller	Remote and USB
Picture Format	jpeg
Video Format	MPEG4

Printer Support	Pictbridge and DPOF
Mount	C Mount
Power Supply	DC 12 V, 1.5 A
Weight	1.4 lb

