

# LM301A


# Single Operational Amplifier

#### **Features**


- Short circuit protection and latch free operation
- Slew rate of 10V/µs as a summing amplifier
- Class AB output provides excellent linearity
- · Low bias current

### **Description**


The LM301A is a general purpose operational amplifiers which are externally phase compensated, permit a choice of operation for optimum high frequency performance at a selected gain: unity gain compensation can be obtained with a single capacitor.



## **Internal Block Diagram**



## **Schematic Diagram**



## **Absolute Maximum Ratings**

Parameter	Symbol	Value	Unit	
Supply Voltage	Vcc	±18	V	
Differential Input Voltage	VI(DIFF)	30	V	
Input Voltage	VI	±15	V	
Output short Circuit Duration	-	Continuous	-	
Power Dissipation	PD	500	mW	
Operating Temperature Range	Topr	0 ~ +70	°C	
Storage Temperature Range	TSTG	- 65 ~ + 150	°C	

## **Electrical Characteristics**

(TA =+25 $^{\circ}$ C, VCC = +15V, VEE= -15V, unless otherwise specified)

Deversation	Councile of	Conditions		LM301A		l lee it	
Parameter Symbol		Conditions		Min.	Тур.	Max.	Unit
Input Offset Voltage	\ / <sub>1</sub> -	Rs <u>&lt;</u> 50KΩ		-	2.0	7.5	mV
	VIO		Note 1	-	-	10	mV
Input Offset Current	liO		•	-	4.5	50	nA
			Note 1	-	-	70	nA
Input Bias Current	IBIAS			-	60	250	nA
			Note 1	-	-	300	nA
	Icc	Vcc = ± 20V		-	-	•	mA
Supply Current		VCC = ± 15V		-	2.0	3.0	mA
		$V_{CC} = \pm 20V, T$	A = TA(MAX)	-	-	•	mA
Large Signal Voltage Gain	GV	$V_{CC}$ = ± 15V, RL≥2KΩ, $V_{O(P-P)}$ = ± 10V		25	160	-	V/mV
			Note 1	15	-	-	V/mV
Average Temperature Coefficient of Input Offset Voltage (NOTE2)	ΔV10/ΔΤ	Note 1		-	6.0	30	μV/°C
Average Temperature Coefficient	ΔΙΙΟ/ΔΤ	$25 ^{\circ}\text{C} \le \text{T}_{A} \le \text{T}_{A}(\text{MAX})$		-	0.01	0.3	nA/°C
of Input Offset Current (NOTE2)		T <sub>A</sub> (MIN) ≤ T <sub>A</sub> ≤ 25 °C		-	0.02	0.6	nA/°C
Input Voltage Range	VI(R)	Vcc = ± 20V	Note 1	-	-	-	V
		Vcc = ± 15V	Note 1	± 12	-	-	V
Common-Mode Rejection Ratio	CMRR	Rs ≤ 50KΩ	Note 1	70	95	-	dB
Power Supply Rejection Ratio	PSRR	Rs ≤ 50KΩ	Note 1	70	100	-	dB
Output Voltage Swing	VO(P-P)	\/00 - ± 15\/	$R_L = 10K\Omega$	± 12	± 14	-	V
		VCC = ± 15V	$R_L = 2.0 K\Omega$	± 10	± 13	-	V
Input Resistance (NOTE2)	Rı	-		0.5	2.0	-	МΩ

#### Note:

- 1. LM301A:  $0 \le T_A \le +70 \,^{\circ}C$
- 2. Guaranteed by design.

## **Typical Performance Characteristics**




Figure 1. Supply Current




Figure 3. Current Limiting




Figure 5. Power Supply Rejection




Figure 2. Voltage Gain




Figure 4. Input Current





Figure 6. Common Mode Rejection

### **Mechanical Dimensions**

### **Package**

### **Dimensions in millimeters**

## 8-DIP



### **Ordering Information**

Product Number	Package	Operating Temperature
LM301AN	8-DIP	0 ~ + 70 °C

#### **DISCLAIMER**

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

#### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com