

## Printed-circuit board connector - DFK-PC 4/12-G-7,62-LOE - 1830842

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 15 A, Rated voltage (III/2): 400 V, Number of positions: 12, Pitch: 7.62 mm, Connection method: Solder connection, Color: green, Contact surface: Tin, Assembly: Soldering

### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 051488
Weight per Piece (excluding packing)	23.84 GRM
Custom tariff number	85366990
Country of origin	Poland

### Technical data

#### Dimensions

Pitch	7.62 mm
Dimension a	83.82 mm

#### General

Range of articles	DFK-PC 4/..-G -LOE
Rated surge voltage (III/3)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	400 V
Rated voltage (III/2)	400 V
Rated voltage (II/2)	800 V
Connection in acc. with standard	EN-VDE
Nominal current $I_N$	15 A
Insulating material	PA
Color	green
Number of positions	12

### Classifications

eCl@ss

eCl@ss 4.0	272607xx
------------	----------

## Printed-circuit board connector - DFK-PC 4/12-G-7,62-LOE - 1830842

### Classifications

#### eCl@ss

eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

#### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

#### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409