
# **3M<sup>TM</sup> Scotchlok<sup>TM</sup> Terminals**

MU20-110DF-A, MU20-110/32DF-A, MU18-110DF-A, MU14-110DF-A Female Disconnect, Non-Insulated, Butted Seam



## **Data Sheet**

# September 2008

Product Number	Wire Range (AWG)	Mates with <u>Male Tab</u> Width (W') X Thickness	L	Barrel Length	Barrel I.D.
MU20-110DF-A	26-22	0.110 x 0.020	.50	.17	.04
MU20-110/32DF-A	26-22	0.110 x 0.032	.50	.17	.04
MU18-110DF-A	22-18	0.110 x 0.020	.53	.20	.08
MU14-110DF-A	16-14	0.110 x 0.020	.53	.20	.10

#### **Specifications**

Wire Size.: Barrel Seam: Maximum Current: Terminal Material: Plating: See table above Butted Same as wire Brass Tin

Installation Information

### 

Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

For use on stranded copper wire only.

Strip away the end 1/4 inch of wire insulation.

Make the crimp the proper station of a recommended 3M<sup>™</sup> Scotchlok<sup>™</sup> Crimp Tool: TH-440, TH-450 (scissor style) or TR-490 (ratchet style) hand tools.



Barrel Crimp (Electrical)



# **3M<sup>™</sup> Scotchlok<sup>™</sup> Terminals** MU20-110DF-A, MU20-110/32DF-A, MU18-110-DF-A, MU14-110DF-A

Engineering/ Architectural Specifications	Crimp-Type Female Disconnect Terminals shall, electrically and mechanically, connect permanently to a pre-stripped end of a stranded copper wire, and have a tongue portion with fingers which grip a Male Disconnect in a separable, reusable manner, forming a Quick connect Wiring Termination.				
	The connector line shall offer tongue variations (sized to grip Male Tabs: $0.110' \times 0.020''$ or $0.110'' \times 0.032''$ ) and barrel variations construction (non-insulated, vinyl insulated with insulation grip, nylon fully insulated, etc.).				

Important Notice	All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.
Warranty; Limited Remedy; Limited Liability:	This product will be free from defects in material and manufacture at the time of purchase. <b>3M</b> <b>MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED</b> <b>WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.</b> If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.

3M and Scotchlok are trademarks of 3M Company.



Electrical Markets Division 6801 River Place Blvd. Austin, TX 78726-9000 800 245 3573 FAX 800 245 0329 www.3M.com/electrical

Please recycle. © 3M 2008 All rights reserved. 78-8127-6997-0\_A