

Control cabinet - FB-8-AL - 2316200

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Aluminum field junction box with 8 ports for use in hazardous locations. Includes FB-ET trunk module, Plugtrab base with option for surge protection plug, and DIN rail space for up to 6 device couplers.

Product Features

- ✓ Developed specifically for field device coupler systems
- ✓ Cable glands, plugs, and breather must be ordered separately
- ✓ Each housing has M20 ports and can be configured as desired
- ✓ Entries for the trunk line (input/output) and breather connections
- ✓ Includes an FB-ET trunk line module and enables the installation of additional couplers and PT plugs
- ✓ Busbar and shield clamps



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	5270.743 GRM
Custom tariff number	85371010
Country of origin	United States

Technical data

Dimensions

Width	202 mm
Height	232 mm
Depth	111 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Degree of protection	IP66 / NEMA 4X

Control cabinet - FB-8-AL - 2316200

Technical data

General

Mounting position	Vertical
Net weight	3220 g
Housing material	Aluminum, die-cast, corrosion resistant, powder-coated
ATEX	# II 2 G/2 D

Classifications

eCl@ss

eCl@ss 4.0	27250203
eCl@ss 4.1	27250203
eCl@ss 5.0	27250203
eCl@ss 5.1	27259205
eCl@ss 6.0	27242610
eCl@ss 7.0	27242610
eCl@ss 8.0	27242610

ETIM

ETIM 3.0	EC001600
ETIM 4.0	EC000261
ETIM 5.0	EC000261

UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	43201553

Drawings

Control cabinet - FB-8-AL - 2316200

Dimensioned drawing

