

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Polyamide protective hose, inflammability class HB, UV resistant

Image shows WP-PA HF-HB 10.0 BK version

Key Commercial Data

Packing unit	1 M
Minimum order quantity	50 M
Custom tariff number	39173200
Country of origin	Germany

Technical data

Dimensions

Inner diameter (f)	10.00 mm
Outside diameter	13.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C 105 °C
Short-term temperature	120 °C

General

Color	black
Туре	Helically corrugated plastic hose
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	НВ
Material	PA
Bending radius, static	20.00 mm
Bending radius, dynamic	45.00 mm

Standards and Regulations

Resistance to UV radiation	yes
Halogen-free	yes



Technical data

Standards and Regulations

Connection in acc. with standard	UL
Flammability rating according to UL 94	НВ

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27430304

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

UL Recognized / VDE Zeichengenehmigung

Ex Approvals

Approvals submitted



Approvals

Approval details

UL Recognized **5**

VDE Zeichengenehmigung



Accessories

Accessories

Corrugated pipe screw connection

Screw connection - WP-G HF IP66 PG9 BK - 3240889



Cable gland, Pg thread, IP66 protection, straight

Screw connection - WP-G HF IP66 M12 BK - 3240896



Cable gland, metric thread, IP66 protection, straight

Screw connection - WP-G HF IP69K PG9 BK - 3240875



Cable gland, Pg thread, IP68/69k protection, straight



Accessories

Screw connection - WP-G HF IP69K M12 BK - 3240882



Cable gland, metric thread, IP68/69k protection, straight

Screw connection - WP-GA HF IP66 PG9 BK - 3240917



Cable gland, Pg thread, IP66 protection, angled

Screw connection - WP-GA HF IP66 M12 BK - 3240924



Cable gland, metric thread, IP66 protection, angled

Screw connection - WP-GA HF IP69K PG9 BK - 3240903



Cable gland, Pg thread, IP68/69k protection, angled

Screw connection - WP-GA HF IP69K M12 BK - 3240910



Cable gland, metric thread, IP68/69k protection, angled



Accessories

Screw connection - WP-GR HF IP66 PG9 BK - 3240945



Cable gland, Pg thread, IP66 protection, with strain relief

Screw connection - WP-GR HF IP66 M12 BK - 3240952



Cable gland, metric thread, IP66 protection, with strain relief

Screw connection - WP-GR HF IP69K PG9 BK - 3240931



Cable gland, Pg thread, IP68/69k protection, with strain relief

Screw connection - WP-GR HF IP69K M12 BK - 3240938



Cable gland, metric thread, IP68/69k protection, with strain relief

Mounting material

Hose holder with cover - WP-BASE C PA HF 13,0 BK - 3240959



Hose holder with cover



Accessories

Hose clamp - WP-BASE HF 13 - 3240966



Hose clamps

Protective cap

Transition sleeve from hose to cable - WP-EC TPE HF 13,0 BK - 3240975



End sleeves, transition sleeves, from hose to cable

Cable protection end sleeve - WP-SC PA HF 13,0 BK - 3240982



End sleeves as cable protection

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com