


Overview

## PANDUCT® Divider Wall



- Wiring duct divider wall can be mounted inside any type of PANDUIT® PVC wiring duct to create multiple channels
- Simply install the divider wall base when mounting the duct and snap the divider wall onto the mounting base accessory (see page E6)
- All versions snap onto DB-C mounting base
- Divider wall heights 2" and greater have a scoreline feature allowing sections to be removed leaving a smooth edge
- Meets UL508/508A insulation material requirement for barrier between conductors





 Slotted Divider Wall for use with all Types of PVC Wiring Duct

 SD2H6
 2.00
 6
 120
 6

 SD3H6
 3.00
 6
 120
 6

 SD4H6
 4.00
 6
 120
 6



Part Number	For Nominal Duct Height (mm)	Std. Pkg. Qty.	Std. Ctn. Qty.	Length (M)			
Metric Solid Divider Wall for use with Type MC Duct							
D50H2	50	2	40	2			
D75H2	75	2	40	2			
D100H2	100	2	40	2			

NOTE: Must be used with Mounting Base (DB-C) which is sold separately. Install mounting bases to the duct channel, locate within 2" of each divider wall end and at least every 12" along the length.

## NEW!

## PANDUCT® Type TMC Low Smoke/Low Toxicity Solid Divider Wall



- TMC Divider Wall can be mounted inside TMC Wiring Duct to create multiple channels
- Low smoke, low toxicity and low flammability material
- Simply install the divider wall base when mounting the duct and snap the divider wall onto mounting base (part No. DB-C)

Part Number	For Nominal Duct Height (mm)	Std. Pkg. Qty.	Std. Ctn. Qty.	Length (M)
TMC50DW2	50	2	20	2
TMC75DW2	75	2	20	2

NOTE: Must be used with Mounting Base (DB-C) which is sold separately. Install mounting bases to the duct channel, locate within 2" of each divider wall end and at least every 12" along the length.

Control Panel

Std.

Ctn.

Qty.

120

120

120

120

120

Length

(ft)

6

6

6

6

6

Special Environment

> Voice & Data

Tools & Accessories

Technical Info

Index