

## Screw connection - WP-G BRASS IP65 PG9 - 3241052

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from brass with Pg thread, IP65 protection

The figure shows the WP-G BRASS IP65 M10 version

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
Custom tariff number	74122000
Country of origin	Germany

### Technical data

#### Dimensions

Width (a)	23 mm
Height	30 mm
Wrench size	19.00 mm
Outside diameter	14.00 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Degree of protection	IP65

#### General

Color	Brass
Type	Straight
	Outer thread
Components	Halogen-free
Material	Brass

# Screw connection - WP-G BRASS IP65 PG9 - 3241052

## Classifications

### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	21132007
eCl@ss 5.1	21132007
eCl@ss 6.0	21132007
eCl@ss 7.0	27439210
eCl@ss 8.0	27439203

### ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC001180

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

### Approvals

---

Approvals

VDE Zeichengenehmigung

---

Ex Approvals

---

Approvals submitted

---

### Approval details

VDE Zeichengenehmigung 
--

## Screw connection - WP-G BRASS IP65 PG9 - 3241052

### Accessories

#### Accessories

#### Corrugated pipe

Protective hose - WP-STEEL PVC C 14 - 3240868



Galvanized steel protective hose with PVC coating