

# AC Power Supply - 5VDC. U.S. 2-pin to 2.5mm locking barrel plug. Compatibility: WR11

PART NUMBER: 76000934



## **Input Specifications:**

Rated input voltage rating: 100VAC to 240VAC

Input frequency: 47 Hz to 63 Hz Rated input current: 0.5A MAX Max. in-rush current: <60A cold start

Input Plug Type: 2-pin U.S.

#### **Output Specifications:**

Output Voltage: 5VDC Load current: 3A Max.

Output Plug: 2.5mm locking barrel plug

#### **Environment:**

Operating Temperature: 0°C TO 40° C Storage Temperature: -20°C TO 70° C

### **Dimensions:**

Size: 70 x 45 x 55mm Cord Length: 5ft

© Copyright 1996-2016 Digi International Inc. All rights reserved.