

Crimping pliers - CRIMPFOX CENTRUS 6S - 1213144

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² to 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Product Features

- With a particularly small handle width, the tool fits perfectly in your hand
- Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping
- Pressure lock ensures consistently high quality crimping results







Key Commercial Data

| Packing unit | 1 pc |
|--------------------------------------|----------|
| Weight per Piece (excluding packing) | 460.0 g |
| Custom tariff number | 82032000 |
| Country of origin | Sweden |

Technical data

Dimensions

| Length (b) | 180 mm |
|------------|--------|
| Width (a) | 70 mm |

General

| Color | black |
|-----------------|------------------------------------|
| Compression | Square crimp |
| Type of contact | Insulated and uninsulated ferrules |
| Designation | Crimping position 1 |



Crimping pliers - CRIMPFOX CENTRUS 6S - 1213144

Technical data

General

| Min. cross section | 0.14 mm² |
|--------------------|----------|
| Max. cross section | 6 mm² |
| AWG min | 26 |
| AWG max | 10 |

Classifications

eCl@ss

| eCl@ss 5.0 | 21040301 |
|------------|----------|
| eCl@ss 5.1 | 21040301 |
| eCl@ss 6.0 | 21043811 |
| eCl@ss 8.0 | 21049090 |

ETIM

| ETIM 4.0 | EC000168 |
|----------|----------|
| ETIM 5.0 | EC000168 |

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Phoenix Contact 2016 @ - all rights reserved http://www.phoenixcontact.com