

## Adapter - EM RD-ADAPTER - 2902747

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Adapter for mounting short circuit-proof hybrid motor starters of type ELR-H51 ... on 35 mm DIN rails.



### Key commercial data

Packing unit	1 PCE
Custom tariff number	85389099
Country of origin	Germany

### Technical data

Product type	Assembly adapter
Approval	UL Listed
	cUL Listed
	IECEE CB Scheme
	cULus Listed

### Classifications

#### eCl@ss

eCl@ss 4.0	27142001
eCl@ss 4.1	27142001
eCl@ss 5.0	27142001
eCl@ss 5.1	27141140
eCl@ss 6.0	27141140
eCl@ss 7.0	27141140
eCl@ss 8.0	27141140

#### ETIM

ETIM 3.0	EC000035
ETIM 4.0	EC002498

# Adapter - EM RD-ADAPTER - 2902747

## Classifications

### ETIM

ETIM 5.0	EC002498
----------	----------

### UNSPSC

UNSPSC 6.01	30211915
UNSPSC 7.0901	39121514
UNSPSC 11	39121514
UNSPSC 12.01	39121514
UNSPSC 13.2	39121514

## Approvals

### Approvals

---

#### Approvals

UL Listed / cUL Listed / IECCE CB Scheme / cULus Listed

---


#### Ex Approvals


---


#### Approvals submitted

---

## Approval details

UL Listed 
---

cUL Listed 
--

IECEE CB Scheme 
---

## Adapter - EM RD-ADAPTER - 2902747

### Approvals

cULus Listed 

### Accessories

#### Additional products

Hybrid motor starter - ELR H51-IESSC-24DC500AC-06 - 2902746



Short-circuit-proof "4 in 1" hybrid motor starter for reversing 3~ AC motors up to 550 V AC, with 24 V DC input, 0.6 A output current, emergency stop function, and adjustable overload shutdown. Can only be used with EM-RD or EM-RI adapter.

Hybrid motor starter - ELR H51-IESSC-24DC500AC-2 - 2902744



Short-circuit-proof "4 in 1" hybrid motor starter for reversing 3~ AC motors up to 550 V AC, with 24 V DC input, 2.4 A output current, emergency stop function, and adjustable overload shutdown. Can only be used with EM-RD or EM-RI adapter.

Hybrid motor starter - ELR H51-IESSC-24DC500AC-9 - 2902745



Short-circuit-proof "4 in 1" hybrid motor starter for reversing 3~ AC motors up to 550 V AC, with 24 V DC input, 9 A output current, emergency stop function, and adjustable overload shutdown. Can only be used with EM-RD or EM-RI adapter.