swissbit®

	SFSA960GQ2AK4TO-C-8C-226-STD	SFSA960GQ2AK4TO-I-8C-226-STD
	swissbit° 960GB F© C€ (™) ∑ 2.5″ Industrial Solid State Disk	swissbit* 960GB © Ž 2.5" Industrial Solid State Disk
Туре	SATA: 2.5"	SATA: 2.5"
Product Family	X-75	X-75
Flash Type	3D TLC	3D TLC
Density	960 GB	960 GB
Temp. Grade	0 to 70°C	-40 to 85°C
Status	in Production	in Production
For new design	Yes	Yes
Rel Cost	1	1
Online Availability		
Endurance Rnd.	2	2
Endurance Seq.	2	2
Perf. Seq. RD [MB/s]	565	565
Perf. Seq. WR [MB/s]	495	495
Perf. Rnd. RD [IOPS]	74100	74100
Perf. Rnd. WR [IOPS]	68200	68200