
72405S

Regular compression spring in 302/304 Stainless Steel with 5.1 total coils and Closed & Ground ends. This spring features an O.D. of 0.975 Inch, an I.D. of 0.783 Inch, and a spring rate of 48 Pound Force per Inch.



View Spec Sheet

Brand	Century Sprin	g	
Display Name	72405S		
Ends	Closed & Grou	Closed & Ground	
Finish	None		
Free Length	1.25 in		
Inside Diameter	0.783 in		
Material	302/304 Stainl	302/304 Stainless Steel	
Outside Diameter	0.975 in	Have a question? Ask an Expert!	
Part Type	Standard		
Rate	48 lbf/in		
Solid Length	0.486 in		
Suggested Max Deflection	0.562 in		

Suggested Max Load	27 lbf
Total Coils	5.1000
Wire Diameter	0.095 in

PRODUCT OPTIONS

Optional Finish
None
Passivation

Have a question? Ask an Expert!

