

# Han 1A-3+PE-c-f latch



Part number	09 10 003 3300
Specification	Han 1A-3+PE-c-f latch
HARTING eCatalogue	https://b2b.harting.com/09100033300

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Inserts
Series	Han <sup>®</sup> 1A

#### Version

Termination method	Crimp termination
Gender	Female
Locking type	Snap-in latches
Size	1 A
Number of contacts	3
PE contact	Yes
Details	Please order crimp contacts separately.  Order separately the single wire seal or the hoods/housings for an IP65 performance.
Details	A Han <sup>®</sup> 1A configuration that only consists of inserts (with or without strain relief, 09 10 000 5300) is an unenclosed connector. In this case protection against electric shock must be provided by the installation methods of the user.
	Contact inserts must not be coupled or decoupled under electrical load.  Contact inserts must not be powered-up in the un-mated condition.

#### Technical characteristics

Conductor cross-section	0.14 4 mm²
Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3

This product is not orderable anymore. Contact your local distribution partner for alternatives.



### Technical characteristics

Insulation resistance	>10 <sup>8</sup> Ω
Limiting temperature	-30 +90 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP20

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

# Specifications and approvals

	EN 45545 0 D00 111 4 111 0 111 0
Specifications	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
	IEC 61373 Category 1 Class B
	EN 60664-1
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	11.2 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors