
Part #: MALLORY Mallory Sonalert Products, Inc. SC628D-1R **Sales Outline Drawing** Revision:

Specifications:	Not for use in new designs - see P/N SC628D-BTR
Sound Level Category	Medium
Mode of Operation	Continuous
Voltage Rating	6 to 28 VDC
Frequency	2000 ± 500 Hz
Loudness @ 2 FT	67 to 80 dB(A) Typ
Current Draw	5-18mA
Housing Material	6/6 Nylon, Col C Biac
Storage Temperature	-40° tr -0 1°
Operating Temperature	-30° to 6' C
Panel Mounting	Recommended hole size is 1.25"(31.75) Thread fro (w) (at standard 30mm(1.181") hole.
Knurled Nut	Used to attach part to paren. he max rec n m or ed torque is 10 in-lbs.
Weight (Typical)	1.6 oz (4 s
NEMA 3R,4X, & 12	ruved with use (CC03.
Options	Please on c factory.

Dimensions: Inches (mm)

ROHS Compliant



MOUNTING: REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 1.25"
HOLE PUNCHED IN PANEL, IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS
ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.