1.90.690.345/0000



RR/

Electrical characteristics of LED	
Max. current, I _F	
	15 mA
LED wavelength typ.	621
Forward voltage typ. U _F at I _F	
	24
LED breakdown voltage U _R bei I _F	
	24
Light intensity	600
Other specifications	
Socket	BA 9 s
Color	white
Ambient temp. operating min.	<u>-30 °C</u>
Ambient temp. operating max.	<u>+65 °C</u>
ROHS compliant	yes
REACH compliant	yes