




Easy LCD Interface

A Plug-and-Play Family of Intelligent Touch Screen Displays for use with your Single Board Computer



Plug and Play Embedded Display

- Works with most Single Board Computers
- Multiple screen sizes and touch screen options
- 10+ year channel life
- Plug-and-play, only 3 connections:
 - HDMI
 - USB
 - Power







- Family of products in sizes from 4.3" to 15.0"
- Plug and play units are interchangeable for easy upgrades
- SBC display customers who don't want to design with bare glass
- ELI can be quickly customized for specific applications

















Target Customers & Applications

- Customers using Linux or Windows Operating Systems
- Users of Single Board Computers like Raspberry Pi, BeagleBone Black, Linux, Android, i.MX or Intel... any SBC with an HDMI output.
- Low cost, plug-and-play solution, so simple to use
- Avoid NRE and shorten your design cycle with ELI























Availability and Support

- ELI is the **Easy LCD Interface**
- Supported by our US based team of engineers
 - ➤ Also Distribution FAE's and Display Specialists
- Stocked at four fully franchised distributors













ELI43-Cx Commercial Series

- 4.3" WQVGA Plug and Play Solution
- Brightness up to 470 nits (typ)
- Viewing Angles of 70/50/70/70° U/D/L/R
- Operating temp range -20 to +70 C
- Cost effective solution
- Two touch screen options:

ELI43-CP PCAP touch screen,

ELI43-CR 4-wire resistive touch screen,





ELI70-CR

- 7.0" WVGA Plug and Play Solution
- Cost effective commercial version
- Brightness 250 nits
- 500:1 Contract Ratio
- Viewing Angles of 60/70/70° U/D/L/R
- Operating temp range -20 to +70 C
- 4-wire resistive touch screen





ELI70-IxHW Rugged HB Series

- 7.0" WVGA Plug and Play Solution
- High Bright Displays up to 800 nits
- IPS Viewing Angles of 85° in every direction
- Wide -30 to +80 C operating temp range
- Automotive grade display for shock and vibration
- Three touch screen options:

ELI70-IPHW PCAP touch screen

ELI70-IRHW 4-wire resistive touch screen,

ELI70-INHW no touch screen,





ELI101-CxW Series

- 10.1" WXGA (1280x800) Plug and Play Solution
- IPS Viewing Angles of 85° in every direction
- Brightness 240 nits
- 800:1 Contrast Ratio
- Operating temp range 0 to +50 C
- Two touch screen options:

ELI101-CPW PCAP touch screen,

ELI101-CNW no touch screen,







ELI121-CxW Series

- 12.1" XGA (1024x768) Plug and Play Solution
- Wide MVA Viewing Angles of 70/70/80/80° U/D/L/R
- Brightness 425 nits
- 700:1 Contrast Ratio
- Operating temp range -30 to +70 C
- Three touch screen options:

ELI121-CPW PCAP touch screen,

ELI121-CRW 4-wire resistive touch screen,

ELI121-CNW no touch screen,

