

## Coupler connector - HC-28S1N1290DU - 1590434

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Coupler connector, straight, Screw locking, M27, Number of positions: 28, Type of contact: Socket, Solder connection, shielded: yes, Cable diameter: 2 mm...14.5 mm

The figure shows the 26-pos. product version



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	92.42 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### General

Type of locking	Screw locking
Insertion/withdrawal cycles mechanical	50
Direction of rotation of contact chamber numbering	Standard
Coding	N
Contact connection method	Solder connection
Type of contacts	Socket
Number of positions	26
Contact diameter of power contacts	1 mm
Litz wire cross section of power contacts min.	0.08 mm <sup>2</sup>
Litz wire cross section of power contacts max.	1 mm <sup>2</sup>
Nominal current per power contact at 25°C	8 A
Conductor entry	2 mm ... 14.5 mm
Pg housing screw connection	none

#### Ambient conditions

# Coupler connector - HC-28S1N1290DU - 1590434

## Technical data

### Ambient conditions

Ambient temperature	-20 °C ... 125 °C
Degree of protection	IP67, when plugged in

### Material

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA66
Contact material	CuZn
Contact surface	Nickel-plated, gold coating
Gasket and O-ring material	FPM

### Specifications according to DIN EN 61984:2001

Installation height max.	2000 m
Nominal / operating voltage of power contacts	150 V
Rated surge voltage of power contacts	1.5 kV
Overvoltage category of power contacts	II
Degree of pollution of power contacts	3
Overvoltage category of signal contacts	II
Degree of pollution of signal contacts	3

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440102

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002641

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015

# Coupler connector - HC-28S1N1290DU - 1590434

## Classifications

### UNSPSC

UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

## Approvals

### Approvals

---

### Approvals

### EAC

---

### Ex Approvals

---

### Approvals submitted


---

## Approval details


EAC
-----

## Drawings

Schematic diagram




Diagram



## Coupler connector - HC-28S1N1290DU - 1590434

Dimensional drawing



---

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>