

ARCA 203015 No MP



Sample image

Order symbol : ARCA 203015 No MP

Product nr : 8120020N

UL Code : UL508A

Description : Cabinet, PC

Remarks : Grey cover, 1-point locking, hinges on the short side

EAN : 6418074089403

El. number :

- Finland : 3424557
- Denmark : 8212097450

Including : Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.

Dimensions :	Height	Width	Depth
mm :	200	300	150
inch :	11.81	7.87	5.91

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Accessories :

MPMP ARCA 3020	Mounting plate multiperforated (250x150x2 mm - ø3.6 mm)
IDS ARCA 2030	Inner door set
MPP ARCA 2030	Mounting plate perforated (250x150x2 mm - 26x11 mm)
MPS ARCA 3020	Mounting plate (250x150x2 mm) (250 x 150 x 2)
DRS ARCA 203015	DIN rail frame set (285 x 185 x 35)
RCS ARCA 2030	Rain canopy set for size 2030
PMK ARCA 30	PoleMounting kit, for pole ø100-300mm (385 x 285 x 35)
MPX ARCA 3020	Mounting plate (250x150 mm) (250 x 150 x 15)

Ratings :

Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK10;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C

Flammability Rating :	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C :	960C
UL Type	NEMA__1_4_4X_12_13