

PRODUCT DATASHEET

Button Tag – D10

Small Tag to fit into Small Space

Overmolded Metal Tag features its ultra small size in just 10mm diameter. This tag is built with Industrial-grade plastic to withstand harsh conditions. It can be mounted on non-metal items by Using adhesive or put in product identification purpose.

Features

- Ultra small size
- IP68 rated

Applications


- Product Identification
- Item-level Tracking




RF Specification	
ІС Туре	NXP I CODE SLIX
Memory	UID 64 bit
	User memory 896 bit
RF Interface Protocol	ISO 15693 / ISO 18000-3
Operating Frequency	13.56 MHz
Applicable Surface	Non - Metal

Environmental Resistance

Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +90°C
Weight	0.3g
Warranty	One Year



*HF sensitivity shown in the figure is measured by Voyantic Tagformance HF Loop Antenna C60. Actual sensitivity performance is subject to the environment in practice.



Physical Specification	
Color	Black
Material	Nylon
Size	D 10 mm/ 0.39 in
	Thickness 1.8 mm/ 0.07 in
	*The exact size is mainly based on metric unit.
IP Rating	IP68
Attachment	Adhesive

Ref. No: Digi-Key / 420580527-01058

All rights reserved. Product specifications are subject to change without prior notification.

Securitag Assembly Group (SAG) reserves the rights to change product specifications without prior notice. Our products are free from defects in material and workmanship. However, this warranty does not cover accidental damage, wear and tear due to Under no conditions is SAG liable for loss and damage to a device, data or records. We also recommend extra care to minimize ESD improper use. in the surroundings of the application.

