

PRODUCT DATASHEET

NFC Ferrite Tag 0503 - F

Embed to Empower Your Small Device with NFC Functions

0503 (size in 5x3mm) Ferrite Tag features its small and compact size. It can be embedded to an item to instantly empower it with NFC function. Meanwhile, Ferrite Tag has superior heat tolerance to survive extreme use condition.


Features


- Ultra small in size
- Great resistibility to high/low temperature
- On-Metal or Non-Metal type available

Applications

- Product Identification
- Item-level Tracking








ST25TV02K
EEPROM 2 kbit
ISO/ ICE 15693
13.56 MHz
Non - Metal

Physical Specification	
Material	Ferrite
Size	L 4.9 mm/ 0.19 in
	W 3.0mm/ 0.11 in
	Thickness 2.5mm/ 0.09 in
	*The exact size is mainly based on metric unit.
IP Rating	IP65
Attachment	SMD Process / Insert molding Applicable



*HF sensitivity shown in the figure is measured by Testram UD Loop Antenna 13phi. Actual sensitivity performance is subject to the environment in practice.

Environmental Resistance	
Operating Temperature	-40°C to +85°C
Storage Temperature	-60°C to +200°C
Warranty	One Year

Ref. No: Digi-ley / 420970816-02299

All rights reserved. Product specifications are subject to change without prior notification.

Securitag Assembly Group (SAG) reserves the rights to change product specifications without prior notice. Our products are free from defects in material and workmanship. However, this warranty does not cover accidental damage, wear and tear due to Under no conditions is SAG liable for loss and damage to a device, data or records. We also recommend extra care to minimize ESD improper use. in the surroundings of the application.

