

## 24/7 FLASHING BLINKERSTOP®





**13W SOLAR PANEL 14Ah BATTERY CAPACITY** 



**13W SELF-CONTAINED TOP-OF-POLE SOLAR CABINET 28Ah BATTERY CAPACITY** 





## **SYSTEM SPECIFICATIONS**

J . J . L	
SIGN LEGEND	R1-1
DIMMING	Variable based on photocell sensor input or 6V solar panel
LED TYPE	Red environmentally-sealed, high-power LED
LED LIFE EXPECTANCY	100,000 hours
VISIBILITY	Daytime: more than 1,000 feet Nighttime: more than 1 mile
ENCLOSED ALUMINUM CHANNELS	Protect wiring against inclement weather, tampering and vandalism
AUTONOMY	30+ days (when applicable)
OPERATING TEMPERATURE RANGE	-40°F to 122°F (-40°C to 50°C)
DIMENSIONS	24"W x 24"H x 1"D
	30"W x 30"H x 1"D
	36"W x 36"H x 1"D
	48"W x 48"H x 1"D
WARRANTY	3-year limited battery warranty
	5-year limited system warranty
	10-year limited solar panel warranty

(800) 236-0112

