


IBC™ Brand Cleaning Tools for Simplex Connections





- IBC™ Brand Cleaning Tool SC for 2.5mm connectors
- Designed for SC, ST and FC for UPC & APC polishes
- IBC™ Brand Cleaning Tool LC for 1.25 mm connectors
- Designed for standard LC, LC secure key and MU for UPC & APC polishes
- IBCTM Brand Cleaning Tool HC for hardened connectors
- Designed for OptiTap® compatible connector systems

Features

- Easy pushing motion engages and initiates cleaning

- Cleaning system rotates 360° for a full sweep
- Extendable tip reaches recessed connectors
- Audible click when engaged

Arizona Road Dust	Skin Oil
Dryer Lint	Graphite - Pre Mate
Graphite - Post Mate	70% IPA Residue
Distilled H ₂ O Residue	Hand Lotion
NaCl Residue	Vegetable Oil

Applications

- Fiber network panels and assemblies
- Outdoor FTTX applications
- Cable assembly production facility
- Testing laboratories
- Servers, switches, routers and ROADMS with SC, FC, ST and LC interfaces

Environmental Properties

- Crush resistance up to 45lbs
- Impact resistance up to 6 feet
- Operating Temperature Range 10° C to +60°

Ordering Information⁹

Part Number	Description
9392	IBC™ Brand Cleaning Tool SC for 2.5mm connectors - SC, FC and ST for UPC and APC polishes
9393	IBC™ Brand Cleaning Tool LC for 1.25mm connectors - LC, LC secure key and MU for UPC and APC polishes
9394	IBC™ Brand Cleaning Tool HC for hardened connectors - OptiTap® compatible connection systems

For additional information about IBCTM Brand Simplex Cleaning Tools or help finding a local distributor, please contact Customer Service at 828-323-8883 or visit our web site at www.usconec.com

MSCONEC