

PRODUCT DATASHEET

NFC Ferrite Tag 0503 - M


Embed to Empower Your Small Device with NFC Functions

0503 (size in 5x3mm) Ferrite Tag features its small and compact size. It can be embedded to an item to instantly empower it with NFC function. Meanwhile, Ferrite Tag has superior heat tolerance to survive extreme use condition.

Features

- Ultra small in size
- Great resistibility to high/low temperature
- On-Metal or Non-Metal type available





2.4

Applications

- Product Identification
- Item-level Tracking

RF Specification

RF Interface Protocol

Operating Frequency

Applicable Surface

IC Type

Memory

ST25TV02K
EEPROM 2 kbit
ISO/ ICE 15693

Physical Specification		
Material	Ferrite	
Size	L 4.9 mm/ 0.19 in	
	W 3.0mm/ 0.11 in	
	Thickness 2.5mm/ 0.09 in	
	*The exact size is mainly based on metric unit.	
IP Rating	IP65	
Attachment	SMD Process / Insert molding Applicable	


13.56 MHz

On-Metal









*HF sensitivity shown in the figure is measured by Testram UD Loop Antenna 13phi. Actual sensitivity performance is subject to the environment in practice.

Environmental Resistance		
Operating Temperature	-40°C to +85°C	
Storage Temperature	-60°C to +200°C	
Warranty	One Year	

Ref. No: Digi-ley / 420970816-02299



