

## 24/7 FLASHING YIELD BLINKERSIGN®

**YIELD** 

BlinkerSign<sup>®</sup> Flashing LED signs are edge-lit signs engineered to capture drivers' attention and increase roadway compliance with highly visible LEDs.

- Programmed to flash 24 hours a day, 7 days a week with Dusk 'til Dawn options available
- Solar or AC power options to work in any setting
- Lightweight system for simple installation
- MUTCD-compliant, made in the USA
- Ruggedized BlinkerSign<sup>®</sup> upgrade available that can withstand extreme conditions, including falling debris, heavy winds and plowed or blowing snow






13W SOLAR PANEL 14Ah BATTERY CAPACITY



## 13W SELF-CONTAINED TOP-OF-POLE SOLAR CABINET 28Ah BATTERY CAPACITY



120VAC



BACK

## SYSTEM SPECIFICATIONS

SIGN LEGEND	R1-2
DIMMING	Variable based on photocell sensor input or 6V solar panel
LED COLOR	White or red
LED TYPE	Environmentally-sealed, high-power LED
LED LIFE EXPECTANCY	100,000 hours
VISIBILITY	Daytime: more than 1,000 feet Nighttime: more than 1 mile
ENCLOSED ALUMINUM CHANNELS	Protect wiring against inclement weather, tampering and vandalism
AUTONOMY	30+ days (when applicable)
OPERATING TEMPERATURE RANGE	-40°F to 122°F (-40°C to 50°C)
DIMENSIONS	30″W x 30″H x 1″D 36″W x 36″H x 1″D 48″W x 48″H x 1″D
WARRANTY	3-year limited battery warranty 5-year limited system warranty 10-year limited solar panel warranty

(800) 236-0112

TAPCOnet.com

© 2021 Traffic and Parking Control Co., Inc. | 5100 West Brown Deer Rd., Brown Deer WI 53223 | Phone (800) 236-0112 | Fax 800-444-0331 www.TAPCOnet.com