## **1500 Watt Mosorb™ Zener** Transient Voltage Suppressors

## **Unidirectional\***

Mosorb devices are designed to protect voltage sensitive components from high voltage, high–energy transients. They have excellent clamping capability, high surge capability, low zener impedance and fast response time. These devices are ON Semiconductor's exclusive, cost-effective, highly reliable Surmetic<sup>™</sup> axial leaded package and are ideally-suited for use in communication systems, numerical controls, process controls, medical equipment, business machines, power supplies and many other industrial/consumer applications, to protect CMOS, MOS and Bipolar integrated circuits.

#### **Specification Features:**

- Working Peak Reverse Voltage Range 5 V
- Peak Power 1500 Watts @ 1 ms
- Maximum Clamp Voltage @ Peak Pulse Current
- Low Leakage  $< 5 \mu A$  Above 10 V
- Response Time is Typically < 1 ns

#### **Mechanical Characteristics:**

**CASE:** Void-free, transfer-molded, thermosetting plastic **FINISH:** All external surfaces are corrosion resistant and leads are readily solderable

## MAXIMUM LEAD TEMPERATURE FOR SOLDERING PURPOSES:

230°C, 1/16" from the case for 10 seconds **POLARITY:** Cathode indicated by polarity band **MOUNTING POSITION:** Any

#### MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Peak Power Dissipation (Note 1.) @ $T_L \le 25^{\circ}C$	P <sub>PK</sub>	1500	Watts
Steady State Power Dissipation @ $T_L \le 75^{\circ}C$ , Lead Length = 3/8" Derated above $T_L = 75^{\circ}C$	P <sub>D</sub>	5.0 50	Watts mW/°C
Thermal Resistance, Junction-to-Lead	$R_{\thetaJL}$	20	°C/W
Forward Surge Current (Note 2.) @ $T_A = 25^{\circ}C$	I <sub>FSM</sub>	200	Amps
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	– 65 to +175	°C

1. Nonrepetitive current pulse per Figure 4 and derated above  $T_A = 25^{\circ}C$  per Figure 2.


 1/2 sine wave (or equivalent square wave), PW = 8.3 ms, duty cycle = 4 pulses per minute maximum.

\* Bidirectional device will not be available in this device



## ON Semiconductor<sup>™</sup>

http://onsemi.com



YY = Year


## WW = Work Week

#### **ORDERING INFORMATION**

I	Device	Package	Shipping
1N59	08	Axial Lead	500 Units/Box
1N59	08RL4	Axial Lead	1500/Tape & Reel

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25°C unless
otherwise noted, V <sub>F</sub> = 3.5 V Max. @ I <sub>F</sub> (Note 3.) = 100 A)

Symbol	Parameter				
I <sub>PP</sub>	Maximum Reverse Peak Pulse Current				
V <sub>C</sub>	Clamping Voltage @ IPP				
V <sub>RWM</sub>	Working Peak Reverse Voltage				
I <sub>R</sub>	Maximum Reverse Leakage Current @ V <sub>RWM</sub>				
V <sub>BR</sub>	Breakdown Voltage @ I <sub>T</sub>				
Ι <sub>Τ</sub>	Test Current				
١ <sub>F</sub>	Forward Current				
VF	Forward Voltage @ I <sub>F</sub>				



#### **Uni–Directional TVS**

#### ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25°C unless otherwise noted, V<sub>F</sub> = 3.5 V Max. @ I<sub>F</sub> (Note 3.) = 53 A)


	V <sub>RWM</sub>	Vowa			Breakdown Voltage			C (Volts) (Note 7.	)
Device	(Note 5.)	I <sub>R</sub> @ V <sub>RWM</sub>	V <sub>BR</sub> (Note 6.) (Volts)		@ կ				
(Note 4.)	(Volts)	<b>(μΑ)</b>	Min	Nom	Max	(mA)	@ I <sub>PP</sub> = 120 A	@ I <sub>PP</sub> = 60 A	@ I <sub>PP</sub> = 30 A
1N5908	5.0	300	6.0	_	-	1.0	8.5	8.0	7.6

NOTES:

Square waveform, PW = 8.3 ms, Non–repetitive duty cycle.
 1N5908 is JEDEC registered as a unidirectional device only (no bidirectional option)

5. A transient suppressor is normally selected according to the maximum working peak reverse voltage (V<sub>RWM</sub>), which should be equal to or greater than the dc or continuous peak operating voltage level.

6.  $V_{BR}$  measured at pulse test current I<sub>T</sub> at an ambient temperature of 25°C and minimum voltages in V<sub>BR</sub> are to be controlled. 7. Surge current waveform per Figure 4 and derate per Figure 2 of the General Data – 1500 W at the beginning of this group






Figure 5. Typical Derating Factor for Duty Cycle

#### **APPLICATION NOTES**

#### **RESPONSE TIME**

In most applications, the transient suppressor device is placed in parallel with the equipment or component to be protected. In this situation, there is a time delay associated with the capacitance of the device and an overshoot condition associated with the inductance of the device and the inductance of the connection method. The capacitance effect is of minor importance in the parallel protection scheme because it only produces a time delay in the transition from the operating voltage to the clamp voltage as shown in Figure 6.

The inductive effects in the device are due to actual turn-on time (time required for the device to go from zero current to full current) and lead inductance. This inductive effect produces an overshoot in the voltage across the equipment or component being protected as shown in Figure 7. Minimizing this overshoot is very important in the application, since the main purpose for adding a transient suppressor is to clamp voltage spikes. These devices have excellent response time, typically in the picosecond range and negligible inductance. However, external inductive effects could produce unacceptable overshoot. Proper circuit layout, minimum lead lengths and placing the suppressor device as close as possible to the equipment or components to be protected will minimize this overshoot.


Some input impedance represented by  $Z_{in}$  is essential to prevent overstress of the protection device. This impedance should be as high as possible, without restricting the circuit operation.

#### DUTY CYCLE DERATING

The data of Figure 1 applies for non-repetitive conditions and at a lead temperature of 25°C. If the duty cycle increases, the peak power must be reduced as indicated by the curves of Figure 5. Average power must be derated as the lead or ambient temperature rises above 25°C. The average power derating curve normally given on data sheets may be normalized and used for this purpose.

At first glance the derating curves of Figure 5 appear to be in error as the 10 ms pulse has a higher derating factor than the 10  $\mu$ s pulse. However, when the derating factor for a given pulse of Figure 5 is multiplied by the peak power value of Figure 1 for the same pulse, the results follow the expected trend.

#### **TYPICAL PROTECTION CIRCUIT**








### **CLIPPER BIDIRECTIONAL DEVICES**

- Clipper-bidirectional devices are available in the 1.5KEXXA series and are designated with a "CA" suffix; for example, 1.5KE18CA. Contact your nearest ON Semiconductor representative.
- 2. Clipper-bidirectional part numbers are tested in both directions to electrical parameters in preceeding table (except for  $V_F$  which does not apply).
- 3. The 1N6267A through 1N6303A series are JEDEC registered devices and the registration does not include a "CA" suffix. To order clipper-bidirectional devices one must add CA to the 1.5KE device title.

#### **OUTLINE DIMENSIONS**

# **Transient Voltage Suppressors – Axial Leaded**

## **1500 Watt Mosorb**



P

MOSORB CASE 41A-04 ISSUE D

NOTES:

- NOTES:
  DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  CONTROLLING DIMENSION: INCH.
  LEAD FINISH AND DIAMETER UNCONTROLLED IN DIMENSION P.
  041A-01 THRU 041A-03 OBSOLETE, NEW STANDARD 041A-04.

	INCHES		MILLIMETERS			
DIM	MIN MAX		MIN	MAX		
Α	0.335	0.374	8.50	9.50		
В	0.189	0.209	4.80	5.30		
D	0.038	0.042	0.96	1.06		
K	1.000		25.40			
P		0.050		1.27		

## <u>Notes</u>

Mosorb and Surmetic are trademarks of Semiconductor Components Industries, LLC.

**ON Semiconductor** and without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights on the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

#### PUBLICATION ORDERING INFORMATION

#### Literature Fulfillment:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: ONlit@hibbertco.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

JAPAN: ON Semiconductor, Japan Customer Focus Center 4–32–1 Nishi–Gotanda, Shinagawa–ku, Tokyo, Japan 141–0031 Phone: 81–3–5740–2700 Email: r14525@onsemi.com

ON Semiconductor Website: http://onsemi.com

For additional information, please contact your local Sales Representative.