

## LED T 4.5 superbright, green, 24 V

## 1.90.690.332/0000



Electrical characteristics of LED	
Max. current, I <sub>F</sub>	
	13 mA
LED wavelength typ.	630
Forward voltage typ. U <sub>F</sub> at I <sub>F</sub>	
	24
LED breakdown voltage U <sub>R</sub> bei I <sub>F</sub>	
	24
Light intensity	700
Other specifications	
Socket	<u>T 4.5</u>
Color	green
Ambient temp. operating min.	-30 °C
Ambient temp. operating max.	+65 °C
ROHS compliant	yes
REACH compliant	yes