


Our DC Motors are a cost-effective solution for any application. They offer simple integration and come in a variety of sizes. With endless performance combinations, we have a tailored motor solution for you.


Discover alternative solutions!



Specifications	
Motor Type:	Carbon - Brushed
Rated Voltage:	24V DC
Rated Speed:	1,490 rpm
Rated Torque:	0.49 kg.cm
Termination Style:	Terminals

No-Load Speed:	2,000 rpm (+/- 10%)
No-Load Current:	< 300 mA
Stall Torque:	2.3 kg.cm
Max. Power:	11 W
Max. Effiicency:	55%







© 2020 ISL Products International Ltd. Specifications subject to change without notice.

ISL Products International Ltd. • 235 Robbins Ln., Ste 270 • Syosset, NY 11791 • T 516-937-3475 • www.islproducts.com