



PART NO.			"L"
#4-40 THREAD	#6-32 THREAD	#8-32 THREAD	
HTS4-4-48	HTS6-4-48	HTS8-4-48	1/4 (6.4)
HTS4-5-48	HTS6-5-48	HTS8-5-48	5/16 (7.9)
HTS4-6-48	HTS6-6-48	HTS8-6-48	3/8 (9.5)
HTS4-7-48	HTS6-7-48	HTS8-7-48	7/16 (11.1)
HTS4-8-48	HTS6-8-48	HTS8-8-48	1/2 (12.7)
HTS4-9-48	HTS6-9-48	HTS8-9-48	9/16 (14.3)
HTS4-10-48	HTS6-10-48	HTS8-10-48	5/8 (15.9)
HTS4-11-48	HTS6-11-48	HTS8-11-48	11/16 (17.5)
HTS4-12-48	HTS6-12-48	HTS8-12-48	3/4 (19.1)
HTS4-13-48	HTS6-13-48	HTS8-13-48	13/16 (20.6)
HTS4-14-48	HTS6-14-48	HTS8-14-48	7/8 (22.2)
HTS4-16-48	HTS6-16-48	HTS8-16-48	1.00 (25.4)

NOTES:

- MATERIAL: NYLON 6/6 (RMS-48).
FLAME RETARDANT NYLON, UL94-VO (RMS-103).
AVAILABLE BY SPECIAL ORDER ONLY.
TO ORDER, REPLACE "-48" WITH "-103"
- COLOR: NATURAL

<table border="1"> <tr> <td>B</td> <td>CHANGED FILE NUMBER</td> <td>SM 06.14.02</td> </tr> <tr> <td>A</td> <td>FLAME RETARDANT MAT'L RMS-103 ADDED</td> <td>JL 7.5.00</td> </tr> <tr> <td>REV</td> <td>DESCRIPTION</td> <td>ENGR DATE</td> </tr> </table>			B	CHANGED FILE NUMBER	SM 06.14.02	A	FLAME RETARDANT MAT'L RMS-103 ADDED	JL 7.5.00	REV	DESCRIPTION	ENGR DATE	<table border="1"> <tr> <td colspan="4">TITLE: HEX THREADED STANDOFFS</td> <td> </td> <td> </td> <td>DWG IN IN (MM)</td> <td> </td> </tr> <tr> <td>TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1'</td> <td>FILE # HTS</td> <td>DWN: J.B.</td> <td>APP:</td> <td colspan="4">FINAL</td> </tr> <tr> <td>MAT'L: SEE NOTES</td> <td>RE: RICHCO, INC.</td> <td>DT: 01-20-97</td> <td>DT:</td> <td colspan="2">PART #</td> <td colspan="2">PRINT TYPE</td> </tr> <tr> <td colspan="4"> RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060 </td> <td colspan="2">SEE CHART</td> <td colspan="2">CA</td> </tr> </table>				TITLE: HEX THREADED STANDOFFS						DWG IN IN (MM)		TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1'	FILE # HTS	DWN: J.B.	APP:	FINAL				MAT'L: SEE NOTES	RE: RICHCO, INC.	DT: 01-20-97	DT:	PART #		PRINT TYPE		RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060				SEE CHART		CA	
B	CHANGED FILE NUMBER	SM 06.14.02																																													
A	FLAME RETARDANT MAT'L RMS-103 ADDED	JL 7.5.00																																													
REV	DESCRIPTION	ENGR DATE																																													
TITLE: HEX THREADED STANDOFFS						DWG IN IN (MM)																																									
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1'	FILE # HTS	DWN: J.B.	APP:	FINAL																																											
MAT'L: SEE NOTES	RE: RICHCO, INC.	DT: 01-20-97	DT:	PART #		PRINT TYPE																																									
RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060				SEE CHART		CA																																									