

Lilliput TK1330-NP/C/T - 13.3" HDMI Capacitive Touchscreen monitor

Screen Size (diagonal)	13.3 inch
Aspect Ratio	16:9
Native Resolution	1920x1080 (native)
Viewing Angle (degrees)	170° x, 170° y
Brightness Ratio (cd/m2)	300
Contrast Ratio	800:1
Backlight	LED
Video Inputs	HDMI, DVI, VGA, composite
Audio Outputs	Internal Speaker
Touchscreen Technology	Capacitive multitouch, USB
Input Power	DC 12V (Wide Voltage optional - see related items for details)
Operating Temperature	-20 ~ 60 degrees
Mounting Options	VESA 75, VESA 100
Contents Of Box	
Product	1 x TK1330-NP/C/T monitor
Connection Cables	1x HDMI cable, 1x VGA cable, 1 x A/V input cable, A-A USB Cable

Power Adaptor	1x DC 12V plug (available in UK, US and EU style),
Mounts and stands	Optional stands available
Additional accessories	
Dimensions	
Height (mm)	219
Width (mm)	333.5
Depth (mm)	34.5
Weight (g)	1900