

Navigan™ Wireless Commissioner

NWC 300U

Navigan™ Wireless Commissioner NWC 300U enables simple, wireless configuration of compatible EnOcean control-

NWC 300U can be used to associate (link) supported sensors and switches with these controllers to form advanced control systems.

In addition, advanced configuration parameters can be defined using the PC-based user interface.

Configuration settings can be saved and re- n TCM 330U based LED controllers stored or cloned to enable quick configuration of multiple controllers.

Interactive help is available in the form of a guided walk-though process.

Content

- n NWC 300U USB stick
- **n** PC software for download from web page



Compatible Products

Currently the following EnOcean products are compatible with NWC 300U:

- n EISMU
- n LEDRU
- n LEDDU

Order Information



ORDERING CODE S3054-N300

Features overview

Housing size (including cap)	70 mm x 23 mm x 9 mm (27.56" L x 9.06" W x 3.54" H)
Available OEM label size	39 mm x 12 mm (15.35" L x 4.72" W)
USB Connector	Type A
Weight	12g (0.42 oz.)
RF standard	902 MHz ERP2
Antenna	Integrated whip antenna
LED indicator	USB bus activity Power supply
Environment	Indoor use only / 0° to 40° C (32° to 104° F) 20% to 85% relative humidity (non-condensing)
Agency compliance	FCC, IC, RoHS