

UbiBot® Wireless Multi-Sensor Device Series



POE SPLITTER

Output: 12V DC power output (12V 1A, 13w)10/100Mbps ethernet data
Input: IEEE 802.3af (DC 37-57V,15.4W) from poe switch or poe injector
Application: GS1-AETH1RS



SOLAR CELL PANEL

Working Voltage : 5V
Working Current : 2A
Operating Temperature : -20°C - 60°C
Waterproof : IP67
Cell Conversion Efficiency : 18.5%
Dimensions : 340 x 240 x 17mm \pm 0.5
It is used for GS1 series.