

ø22mm Planetary Gear Motor Carbon - Brushed

MOT-IG22GM 1:742

Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are equiped to handle varying loads and are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.



Contact Us for alternative solutions!

Specifications	
Gearhead Type:	Planetary
Motor Type:	Carbon - Brushed
Rated Voltage:	12V DC
Rated Speed:	8 rpm
Rated Torque:	10 kg.cm
Rated Current:	400 mA

No-Load Speed:	11 rpm (+/- 10%)
No-Load Current:	< 200 mA
Stall Torque:	34 kg.cm
Max. Power:	0.94 W
Reduction Ratio:	742:1
Termination Style:	Terminals





